

10X ZEISS A-Plan Objective

See More by [ZEISS](#)



ZEISS A-Plan Objectives



Stock #13-816 3-4 DAYS

⊖ 1 ⊕ **€239,00**

ADD TO CART

Qty 1+
€239,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
0.17

Field of View (mm):
2.3

Focal Length FL (mm):
16.50

Model Number: 421040-9900-000
Length excluding Threads (mm): 40.40
Magnification: 10X
Maximum Diameter (mm): 30
Numerical Aperture NA: 0.25
Mounting Threads: M27 x0.75
Compatible Tube Lens Focal Length (mm): Focal Length: 164.50mm
Type: Microscope Objective
Typical Applications: Fluorescence, BrightField, Polarization-Optical DIC
Resolving Power (µm): 1.1
Depth of Field (µm): 4.40
Operating Temperature (°C): +10 to +40
Operating Humidity: 75% at 35°C
Working Distance (mm): 4.5
Weight (g): 152
Wavelength Range (nm): 480 - 650
Style: Infinity Corrected
Manufacturer: ZEISS
Field Number (mm): 23
Parfocal Length (mm): 45.06
Immersion Liquid: N/A

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View