

TECHSPEC® 1:1 with 30mm and 30mm EFL Achromats, 30mm Achromatic Pair



TECHSPEC Mounted Achromatic Lens Pairs

Stock **#46-002** 3-4 DAYS



1



€227,00

ADD TO CART

Qty 1-5

€227,00

Qty 6+

€181,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
22.0

Center Air Spacing (mm):
0.54

Substrate: ☐
[N-BAF10](#) / [N-SF10](#) / [N-BAF10](#) / [N-SF10](#)

Surface Quality: 40-20
Working f#: f/1.28
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Effective Focal Length EFL A (mm): 30.00
Effective Focal Length EFL B (mm): 30.00
Housing Diameter (mm): 30 +0.0/-0.10
Housing Length (mm): 34 ±0.2
Lens Edge Spacing at Mount (mm): 8
Magnification: 1:1
Object Distance (mm): 19.19
Image Distance (mm): 19.19
Construction: Achromat Pair in Anodized Aluminum Housing
Type: Relay Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View