

TECHSPEC® 1:1.25 with 40mm and 50mm EFL Achromats, 30mm Achromatic Pair



TECHSPEC Mounted Achromatic Lens Pairs

Stock **#46-008** 3-4 DAYS



1



€227,00

ADD TO CART

Qty 1-5

€227,00

Qty 6+

€181,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
22.0

Center Air Spacing (mm):
3.14

Substrate: ☐
[S-BAH11](#) / [N-SF10](#) / [N-BAF10](#) / [N-SF10](#)

Surface Quality: 40-20
Working f#: f/2.26
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Effective Focal Length EFL A (mm): 40.00
Effective Focal Length EFL B (mm): 50.00
Housing Diameter (mm): 30 +0.0/-0.10
Housing Length (mm): 34 ±0.2
Lens Edge Spacing at Mount (mm): 8
Magnification: 1:1.25
Object Distance (mm): 29.31
Image Distance (mm): 39.68
Construction: Achromat Pair in Anodized Aluminum Housing
Type: Relay Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View