

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #25-722 3-4 DAYS



1



€597,00

ADD TO CART

Qty 1-9

€597,00

Qty 10+

€537,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):

25.00 ±0.20

Angle of Incidence (°):

0

Optical Density OD (Average):

≥3.0

Clear Aperture CA (mm):

22.0
Center Wavelength CWL (nm): 11,600.00 ±40
Full Width-Half Max FWHM (nm): 500.00 ±50
Substrate: □ Germanium
Coating: Traditional Coated
Surface Quality: 80-50
Thickness (mm): 1.00 ±0.2
Transmission (%): 80 (minimum)
Type: Bandpass Filter
Typical Applications: Astronomical Mapping
Blocking Wavelength Range (nm): 200 - 14500
Center Wavelength CWL (μm): 11.60 ±0.04
Full Width-Half Max FWHM (μm): 0.50 ±0.05

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant