

[See all 21 Products in Family](#)

## 12-50mm FL, CS-Mount, P-iris, 4K Ultra Motorized with Limit Switch



Image represents #22-806: Design will vary by stock number.

Stock **#22-813** **1 In Stock**

-

1

+

€617<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | €617,00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

**i** Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

### Product Downloads

#### General

User with Motorized Lens Control Board (#22-832)

Note:

Varifocal Lens

Type:

#### Physical & Mechanical Properties

P-iris

Iris Option:

|       |                        |
|-------|------------------------|
| 52.00 | Length (mm):           |
| 61.0  | Maximum Diameter (mm): |
| 71    | Weight (g):            |

Optical Properties

|               |                                               |
|---------------|-----------------------------------------------|
| 36° - 8.6°    | Horizontal Field of View @ Max Sensor Format: |
| 12-50         | Focal Length Range (mm):                      |
| 2000 - ∞      | Working Distance (mm):                        |
| f/1.8- Closed | Aperture (f/#):                               |
| VS            | Lens Wavelength Range:                        |

Sensor

|        |                        |
|--------|------------------------|
| 1/1.7" | Maximum Sensor Format: |
|--------|------------------------|

Threading & Mounting

|          |        |
|----------|--------|
| CS-Mount | Mount: |
|----------|--------|

Regulatory Compliance

|                      |                             |
|----------------------|-----------------------------|
| <a href="#">View</a> | Certificate of Conformance: |
|----------------------|-----------------------------|

Product Details

- 4 - 10mm Focal Length Range for up to 135° Horizontal FOV
- True 4K, 12 Megapixel Resolution
- IR corrected for Day or Night

4K Wide Angle Lenses provide a wide range of fields of view for applications with long working distance requirements, allowing for excellent resolution up to 12 megapixels. Available with DC auto-iris, P-iris, and manual iris versions, these lenses are ideal for a wide range of applications including Intelligent Traffic (ITS), remote sensing, security, and robotics. The lenses are IR corrected for use with true Day/Night cameras, providing a bright image in both visible and IR illumination without manual adjustment. Lens mounting options include S-mount (M12), CS-mount, and C-mount with motorized and non-motorized versions available.