

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Image represents #22-806: Design will vary by stock number.

Stock #22-812 3-4 DAYS



1



€570,00

ADD TO CART

Qty 1+

€570,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Iris Option:
Precise Iris

Length (mm):
52.00

Maximum Diameter (mm):
61.0

Weight (g):
67

Horizontal Field of View @ Max Sensor Format: 36° - 8.6°
Note: User with Motorized Lens Control Board (#22-830)
Type: Varifocal Lens
Maximum Sensor Format: 1/1.7"
Working Distance (mm): 2000 - ∞
Mount: CS-Mount
Aperture (f/#): f/1.8- Closed
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View