

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #21-549 3-4 DAYS



1



€50,00

ADD TO CART

Qty 1-9

€50,00

Qty 10+

€48,20

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Optical Density OD (Average):
1.2

Clear Aperture CA (mm):
18.50

Filter Thread:
M22.5 x0.50

Substrate: ☐

ND Filter Glass
Surface Quality: 40-20
Transmission (%): 6.25
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View