

12", White, UltraSeal Washdown Bar Light

See More by [Advanced Illumination](#)



Advanced Illumination UltraSeal Washdown Bar Lights

Stock **#18-629** 3-4 DAYS

- 1 +

€1.312,00

ADD TO CART

Qty 1+

€1.312,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Color:
White

Input Voltage (V):
24V

Model Number:
AL247M12-WH-IIC

Operating Temperature (°C):
0 - 60

Dimensions (mm): 323.8 x 42.9 x 24
Weight (g): 657
LED Lifetime (hours): 50000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Area Light
Illumination Mode: Constant
Environmental Rating: IP69K
Minimum Input Current: 0.70A

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)