

120 MHz Fiber Coupled Optical Reciever Module



Stock #87-324 3-4 DAYS

- 1 + **€260,00**

ADD TO CART

Qty 1+
€260,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Sensitivity (dBm): -42
Wavelength Range (nm): 1310 - 1550
Connector: FC/PC
Dynamic Range (dB): 25.00
Fiber Diameter (µm): 50/125/245/900

Regulatory Compliance

RoHS:
Not Compliant

Certificate of Conformance:
[View](#)
