

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

1200 Grooves, 25mm Square, 400nm Ruled Diffraction Grating



Reflective Ruled Diffraction Gratings

Stock #41-046 3-4 DAYS



1



€134,00

ADD TO CART

Qty 1+

€134,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):  
1200

Blaze Wavelength (nm):  
400

Blaze Angle (°):  
13.88

Dimensions (mm):  
25.0 x 25.0 ±0.5

|                                                             |
|-------------------------------------------------------------|
| <b>Clear Aperture (%)</b> :<br>90                           |
| <b>Coating:</b><br>Bare Aluminum                            |
| <b>Construction:</b><br>Ruled Grating                       |
| <b>Direction of Grooves:</b><br>Parallel to Short Dimension |
| <b>Length (mm):</b><br>25.00                                |
| <b>Substrate:</b> <input type="checkbox"/><br>Float Glass   |
| <b>Thickness (mm):</b><br>9.50 ±0.5                         |
| <b>Type:</b><br>Reflective Diffraction Grating              |
| <b>Width (mm):</b><br>25.00                                 |
| <b>Alignment of Grooves to Edge (°):</b><br>±0.5            |
| <b>Absolute Peak Efficiency, Typical (%)</b> :<br>73        |
| <b>Peak Efficiency Avg, Typical (%)</b> :<br>>68            |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |

---