

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

1200 Grooves/mm, 12.7 mm Square, VIS Holographic Grating



Reflective Holographic Gratings

Stock #43-773 3-4 DAYS



1



€102,00

ADD TO CART

Qty 1+

€102,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
1200

Wavelength Range (nm):
400 - 700

Dimensions (mm):
12.7 x 12.7 ±0.5

Coating:
Bare Aluminum

Construction: Holographic Grating
Length (mm): 12.70
Substrate: ☐ Float Glass
Thickness (mm): 6.00 ±0.5
Type: Reflective Diffraction Grating
Wavelength: VIS
Width (mm): 12.70
Alignment of Grooves to Edge (°): ±0.5
Absolute Peak Efficiency, Typical (%): 73
Peak Efficiency Avg, Typical (%): >63

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
