

# 1200 Grooves/mm, 25mm Sq, UV Transmission Grating Beamsplitter



Stock #85-295 3-4 DAYS

- 1 + **€232,50**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| €232,50                       |
| Qty 10+                       |
| €209,50                       |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):  
1200

Wavelength Range (nm):  
250 - 450

Blaze Angle (°):  
26.7

|                                                                                           |
|-------------------------------------------------------------------------------------------|
| <b>Dimensions (mm):</b><br>25.00 x25.00                                                   |
| <b>Construction:</b><br>Blazed Grating                                                    |
| <b>Length (mm):</b><br>25.00                                                              |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">Fused Silica</a> (Corning 7980) |
| <b>Thickness (mm):</b><br>2.00 ±0.5                                                       |
| <b>Type:</b><br>Transmission Diffraction Grating                                          |
| <b>Width (mm):</b><br>25.00                                                               |
| <b>Alignment of Grooves to Edge (°):</b><br>±0.5                                          |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |