

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Richardson Gratings™ High Precision Plane Ruled Reflective Diffraction Gratings



Stock #37-136 3-4 DAYS



1



€168,00

ADD TO CART

Qty 1+

€168,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
1200

Wavelength Range (nm):
200 - 1600

Blaze Wavelength (nm):

400 ±25
Blaze Angle (°): 14
Peak Efficiency, Typical (%): 82
Dimensions (mm): 25.0 x 25.0 ±0.1
Clear Aperture (%): >90
Coating: Aluminium
Construction: Ruled Grating
Length (mm): 25.00
Substrate: ☐ Float Glass
Thickness (mm): 6.00 ±0.5
Type: Reflective Diffraction Grating
Width (mm): 25.00
Reflected Wavefront, RMS: λ/4
Centering of Ruled Area on Substrate (mm): ±1
Alignment of Grooves to Edge (°): ±0.15
Groove Spacing Tolerance (%): <0.05
Polarization: Unpolarized
Master Reference: 1264
Spectral Order (m): 1

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View