

TECHSPEC®

12.0mm Dia. x 42.0mm FL, VIS-EXT, Inked, Plano-Convex Lens



Stock **#88-678-INK** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

€54,00

ADD TO CART

Qty 1-9
€54,00
Qty 10+
€48,50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.00 ±0.025

Effective Focal Length EFL (mm):

42.00 @ 587.6nm
Back Focal Length BFL (mm): 40.22
Coating: VIS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.70 ±0.05
Edge Thickness ET (mm): 1.85
Radius R₁ (mm): 21.71
Clear Aperture CA (mm): 11
f/#: 3.5
Numerical Aperture NA: 0.14
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 700
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View