

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

12.0mm FL, IR-Cut Filter at 650nm, 1/2, Micro Video Lens



Stock #66-893 3-4 DAYS

[Similar Products](#)



1



€59,00

ADD TO CART

Qty 1-49

€59,00

Qty 50+

€47,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
12.10

Filter Thread:
M12 x 0.50

Maximum Diameter (mm):
14.0

Maximum Image Circle (mm): 6.00
Horizontal Field of View @ Max Sensor Format: 22.2
Resolution, On-Axis: 63 lp/mm @ 20% Contrast
Resolution, 0.7 Field: 60 lp/mm @ 20% Contrast
Resolution, Full Field: 60 lp/mm @ 20% Contrast
Note: IR Cut-Off Filter Included
Type: M12 Imaging Lens
Focal Length FL (mm): 12.00
Maximum Sensor Format: 1/3"
Working Distance (mm): 400 - ∞
Mount: M12 x 0.5 (S-Mbunt)
Aperture (f/#): f/2
Distortion (%): -0.15 @ Full Field
IR Cut Filter: Yes
Lens Wavelength Range: VIS (IR-Cut Filter)

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View