

In order to provide more accurate inventory information, please select your shipping country.

✕

Select Your Country/Region: European Union



SUBMIT



#53-153

Stock #53-153 3-4 DAYS



1



€585,00

ADD TO CART

Qty 1+

€585,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Field of View @ Min Working Distance (mm):
495 - 86

Length (mm):
114.50

Horizontal Field of View, 1/2" Sensor:
27.8° - 4.9°

Filter Thread:
M55.0 x 0.75

Maximum Diameter (mm):

57.00

Weight (g):
475.00

Zoom Ratio:
6:1

Type:
Zoom Lens, Macro

Focal Length FL (mm):
12.50 - 75

Maximum Sensor Format:
2/3"

Working Distance (mm):
1,000 - ∞

Mount:
C-Mount

Aperture (f/#):
f/1.2 - f/16

Lens Wavelength Range:
VS

Regulatory Compliance

RoHS 2015:
[Exempt](#)

Reach 224:
[Contains SVHC\(s\)](#)

Certificate of Conformance:
[View](#)