

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

304.8mm/12.0" Optic Dia., Optical Cell Kinematic Mount



Stock #12-227 3-4 DAYS

- 1 + €5.766,00

ADD TO CART

Qty 1-4

€5.766,00

Qty 5+

€5.373,60

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter of Compatible Optics (mm):
304.8

Clear Aperture CA (inches):
11.5

Clear Aperture CA (mm):

292.1
Thickness of Compatible Optics (mm): 41.05
Optical Centerline (mm): 203.2
Range: 7°
Dimensions (inches): 16.00 x 8.00 x 15.00
Dimensions (mm): 406.4 x 203.2 x 381.0
Weight (lbs): 43.3
Inner Diameter (inches): 12.01
Construction: Black Anodized Aluminum, Stainless Steel
Resolution (inches): 0.031 per turn
Diameter of Compatible Optics (inches): 12
Thickness of Compatible Optics (inches): <1.62
Optical Centerline (inches): 8
Optic Holding Style: Three Spring-Loaded Clips

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View