

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 12.5" Diameter X 125" FL Protected Gold, Parabolic Mirror



Stock #35-730-566 3-4 DAYS

- 1 +

€3.415,00

ADD TO CART

Qty 1-2

€3.415,00

Qty 3+

€2.903,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate:
BOROFLOAT®

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:

N/8
Diameter (inches): 12.5 +0.06/-0
Diameter (mm): 317.50 +1.5/-0
Effective Focal Length EFL (inches): 125.0
Effective Focal Length EFL (mm): 3,175.00
Radius of Curvature (mm): 6,350.00
Aperture (f/#): f/10
Coating: Protected Gold (700-10000nm)
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 286
Edge Thickness ET (inches): 2.13
Edge Thickness ET (mm): 54.10
Type: Parabolic Mirror
Wavelength Range (µm): 0.7 - 10
Wavelength Range (nm): 700 - 10000
Damage Threshold, Reference:  0.8 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant