

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 12.5" Diameter X 75" FL Protected Gold, Parabolic Mirror



Stock #32-276-566 [CONTACT US](#)

-

1

+

 €3.415,00

ADD TO CART

Qty 1-2

€3.415,00

Qty 3+

€2.903,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: ☐ BOROFLOAT®  
☒ SUPREMAX®

Focal Length Tolerance (%):  
±1.5

Surface Quality:  
60-40

Surface Accuracy:

|                                                                                                                  |
|------------------------------------------------------------------------------------------------------------------|
| N/8                                                                                                              |
| <b>Diameter (inches):</b><br>12.5 +0.06/-0                                                                       |
| <b>Diameter (mm):</b><br>317.50 +1.5/-0                                                                          |
| <b>Effective Focal Length EFL (inches):</b><br>75.0                                                              |
| <b>Effective Focal Length EFL (mm):</b><br>1,905.00                                                              |
| <b>Radius of Curvature (mm):</b><br>3,810.00                                                                     |
| <b>Aperture (f/#):</b><br>f/6                                                                                    |
| <b>Coating:</b><br>Protected Gold (700-10000nm)                                                                  |
| <b>Coating Specification:</b><br>R <sub>avg</sub> >96% @ 700 - 2000nm<br>R <sub>avg</sub> >96% @ 2000 - 10,000nm |
| <b>Coating Type:</b><br>Metal                                                                                    |
| <b>Back Surface:</b><br>Ground                                                                                   |
| <b>Clear Aperture CA (mm):</b><br>286                                                                            |
| <b>Edge Thickness ET (inches):</b><br>2.13                                                                       |
| <b>Edge Thickness ET (mm):</b><br>54.10                                                                          |
| <b>Type:</b><br>Parabolic Mirror                                                                                 |
| <b>Wavelength Range (µm):</b><br>0.7 - 10                                                                        |
| <b>Wavelength Range (nm):</b><br>700 - 10000                                                                     |
| <b>Damage Threshold, Reference:</b> <input type="checkbox"/><br>0.8 J/cm <sup>2</sup> @ 1064nm, 10ns             |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |