

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 12.5" Diameter X 75" FL Uncoated, Parabolic Mirror



Stock #32-276-000 3-4 DAYS

1 €2.865,00

ADD TO CART

Qty 1-2

€2.865,00

Qty 3+

€2.435,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: BOROFLOAT® SUPREMAX®

Focal Length Tolerance (%): ±1.5

Surface Quality: 60-40

Surface Accuracy:

N/8
Diameter (inches): 12.5 +0.06/-0
Diameter (mm): 317.50 +1.5/-0
Effective Focal Length EFL (inches): 75.0
Effective Focal Length EFL (mm): 1,905.00
Radius of Curvature (mm): 3,810.00
Aperture (f/#): f/6
Coating: Uncoated
Coating Type: Uncoated
Back Surface: Ground
Clear Aperture CA (mm): 286
Edge Thickness ET (inches): 2.13
Edge Thickness ET (mm): 54.10
Type: Parabolic Mirror

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View