

1.25" x 2.00", IR 940nm, MicroBrite High Intensity Spot Light

See More by [Advanced Illumination](#)



Advanced Illumination MicroBrite High Intensity Spot Lights

Stock **#18-594** 3-4 DAYS

-

1

+

€480,00

ADD TO CART

Qty 1+

€480,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Color:
IR

Model Number:
SL244-940IC

Operating Temperature (°C):
0 - 60

Dimensions (mm):
44.5 x 32.2 x 20.1

Wavelength (nm): 940.00
Weight (g): 168
LED Lifetime (hours): 50000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Length of Cable (m): 2
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Spot Light
Illumination Mode: Constant
Minimum Input Current: 0.14A

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)
