

[See all 60 Products in Family](#)

## TECHSPEC® 125mm, Center Drive, Standard Top, English Extended Micrometer



TECHSPEC® Crossed-Roller Bearing Linear Translation Stages (Standard-Top Model)



Stock #66-452 **3 In Stock**

⊖ 1 ⊕ €850.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-2	€850,00 each
Qty 3+	€744,10 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

English **Type:**

### Physical & Mechanical Properties

Linear (X) **Type of Movement:**



**30mm Standard-Top Stages - Center Drive**



**30mm Standard-Top Stages - Side Drive**



**40mm Standard-Top Stages - Center Drive**



**40mm Standard-Top Stages - Side Drive**




**70mm Standard-Top Stages - Center Drive**



**70mm Standard-Top Stages - Side Drive**



**125mm Standard-Top Stages - Center Drive**



**125mm Standard-Top Stages - Side Drive**

