

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #69-855 3-4 DAYS

[Other Coating Options](#)



1



€195,00

ADD TO CART

Qty 1-5

€195,00

Qty 6+

€156,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
12.50 +0.0/-0.1

Effective Focal Length EFL (mm):  
12.50 @ 587.6nm

Numerical Aperture NA:

|                                                     |
|-----------------------------------------------------|
| 0.50                                                |
| <b>Back Focal Length BFL (mm):</b><br>9.35          |
| <b>Substrate:</b> <a href="#">L-BAL35</a>           |
| <b>Aspheric Design Wavelength (nm):</b><br>587.6    |
| <b>Asphere Figure Error, RMS @ 632.8nm:</b><br>1.2λ |
| <b>Coating:</b><br>Uncoated                         |
| <b>Centering (arcmin):</b><br>≤5                    |
| <b>Surface Quality:</b><br>60-40                    |
| <b>Clear Aperture CA (mm):</b><br>11.25             |
| <b>Edge Thickness ET (mm):</b><br>2.11              |
| <b>Center Thickness CT (mm):</b><br>5.00 ±0.1       |
| <b>f/#:</b><br>1.00                                 |
| <b>Bevel:</b><br>Protective bevel as needed         |
| <b>Shape of Back Surface:</b><br>Plano              |
| <b>Type:</b><br>Aspheric Lens                       |
| <b>Wavelength Range (nm):</b><br>330 - 2400         |
| <b>Conjugate Distance:</b><br>Infinite              |
| <b>Power (diopters):</b><br>80.00                   |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |