

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



TECHSPEC Molded Aspheric Condenser Lenses

Stock **#36-165** ☐ In Stock

[Other Coating Options](#)



1



€27,00

ADD TO CART

Qty 1-10

€27,00

Qty 11+

€24,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.2

Effective Focal Length EFL (mm):
10.00 @ 587.6nm

Numerical Aperture NA:

0.625
Back Focal Length BFL (mm): 4.93
Substrate: ☐ Liba2000+
Focal Length Tolerance (%): ±5
Coating: Uncoated
Centering (arcmin): ≤25
Surface Quality: Molded Side: 5/3 x0.4; E 0.2 Polished Side: 5/3 x0.25; E 0.2
Clear Aperture CA (mm): 11.28
Edge Thickness ET (mm): 3.22
Center Thickness CT (mm): 7.71 ±0.30
f/#: 0.8
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 12.5
Radius R₂ (mm): ∞
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 350 - 2000
Conjugate Distance: Infinite
Note: Click here for more information on the ISO 10110 surface quality specification.

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant