

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 12.5mm Dia. X 25mm FL NIR II Coated Calcium Fluoride PCX Lens



TECHSPEC Calcium Fluoride Plano-Convex (PCX) Lenses

Stock #22-526 3-4 DAYS



1



€190,00

ADD TO CART

Qty 1-5

€190,00

Qty 6+

€152,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.00/-0.10

Effective Focal Length EFL (mm):
25.00 @ 266nm

Back Focal Length BFL (mm):

22.61
Coating: NIR II (750-1550nm)
Substrate: ☐ Calcium Fluoride (CaF ₂)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: λ
Irregularity (P-V) @ 632.8nm: λ/2
Centering (arcmin): <3
Center Thickness CT (mm): 3.50 ±0.1
Edge Thickness ET (mm): 1.66
Radius R₁ (mm): 11.55
Clear Aperture CA (mm): 11.5
f#: 2.00
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 200 - 7000
Axis Orientation: Random

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant