

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 12.5mm Dia -1.00λ Aberration, Spherical Aberration Plate



Spherical Aberration Compensation Plates

Stock #66-754 3-4 DAYS



1



€420,00

ADD TO CART

Qty 1+

€420,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Aberration:

-1.00λ ±λ/16 @ 587nm

Abbe Number (v_d):

64.17

Bevel:

Protective as needed

Clear Aperture (%):

>85

Clear Aperture CA (mm): 11.25
Diameter (mm): 12.50 +0.00/-0.25
Thickness (mm): 3.00 ±0.20
Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.1 (-30 to +70°C) 8.3 (+20 to +300°C)
Density (g/cm³): 2.51
Edges: Fine Ground
Index of Refraction n_d: 1.516
Knoop Hardness (kg/mm²): 610
Parallelism (arcmin): <1
Poisson's Ratio: 0.206
Substrate: N-BK7
Surface Quality: 60-40
Type: Specialty Window
Wavelength Range (nm): 350 - 2200
Young's Modulus (GPa): 82

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View