

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #38-784 [CONTACT US](#)



1



€12,25

ADD TO CART

Qty 1-10

€12,25

Qty 11+

€11,25

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.50 ±0.25

Coating:
Uncoated

Edges:
Ground Edges

Grit: ☐

600

Substrate: ☐
Float Glass

Thickness (mm):
1.60

Type:
Ground Glass Diffuser

Wavelength Range (nm):
350 - 2000

Note:
Sandblasted on first surface

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)
