

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #22-547 3-4 DAYS



1



€195,00

ADD TO CART

Qty 1-5

€195,00

Qty 6+

€156,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
λ/20

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Surface Quality:
20-10

Length of Legs (mm): 12.50
Dimensional Tolerance (mm): +0.00/-0.10
Coating Specification: R_{avg} >95% @ 450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture CA (mm): 15.90 x 11.25
Length of Hypotenuse (mm): 17.70
Type: Right Angle Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Angle Tolerance (arcsec): ±15
Damage Threshold, Reference: 0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant