

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC®  
12.5mm H x 25mm L x -20mm FL Uncoated, Illumination Grade PCV Cylinder Lens



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock #68-054 3-4 DAYS

- 1 + €62,00

ADD TO CART

Qty 1-5

€62,00

Qty 6+

€49,50

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):  
-20.00

Substrate: □  
[N-SF11](#)

Coating:

|                                                 |
|-------------------------------------------------|
| Uncoated                                        |
| <b>Type:</b><br>Cylinder Lens, Plano-Concave    |
| <b>Wavelength Range (nm):</b><br>400 - 2500     |
| <b>Back Focal Length BFL (mm):</b><br>-21.4     |
| <b>Center Thickness CT (mm):</b><br>2.50        |
| <b>Center Thickness Tolerance (mm):</b><br>±0.1 |
| <b>Dimensional Tolerance (mm):</b><br>+0.0/-0.2 |
| <b>Dimensions (mm):</b><br>12.5 x 25.0          |
| <b>Edge Thickness ET (mm):</b><br>3.67          |
| <b>Focal Length Tolerance (%):</b><br>±3        |
| <b>Radius R<sub>1</sub> (mm):</b><br>-15.69     |
| <b>Surface Quality:</b><br>60-40                |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>REACH 201:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |