


In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



TECHSPEC Fused Silica Wedge Prisms

Stock #39-126 CLEARANCE 3-4 DAYS



1



€94,95

ADD TO CART

Qty 1+

€94,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:

Laser V-Coat (1064nm)

Angle Tolerance (arcsec):

30

Bevel:

Protective bevel as needed

Coating Specification:

R_{abs} <0.25% @ 1064nm

Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.52
Design Wavelength DWL (nm): 1064
Diameter (mm): 12.50
Image Orientation: Beam Deviation
Power (diopters): 3.49
Ray Deviation @ 355nm (°): 2.00
Substrate: ☐ Fused Silica (Corning 7980)
Surface Flatness (P-V): λ/10
Surface Quality: 20-10
Thickness (mm): 1.50
Wedge Angle: 4° 11'14"
Note: Specificy this is S1 & S2 power and irregularity, not the overall power of the wedge
Damage Threshold, By Design: ☐ 15 J/cm ² @ 1064nm, 20ns, 20Hz
Power (fringes) @ 632.8nm: 0.50
Irregularity (fringes) @ 632.8nm: 0.20

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View