

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



125mm Micrometer Drive Stage

Stock #66-455 3-4 DAYS



1



€699,00

ADD TO CART

Qty 1-2

€699,00

Qty 3+

€611,80

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Crossed Roller Bearing

Type of Drive:
English Micrometer

Drive Orientation: Side Drive
Type: English
Stage Size (mm): 125 x 125
Travel (inches): 2
Center Hole: 1/4-20
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.635
Load Capacity (kg): 20
Mounting Threads: (21) 1/4-20, (8) 2-56, (4) 6-32
Stage Size (inches): 4.92 x 4.92
Straight Line Accuracy (µm): 2
Pitch (arcsec): 40
Yaw (arcsec): 30

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)
