

[See all 60 Products in Family](#)

**TECHSPEC® 125mm, Side Drive, Standard Top, English Stage**



TECHSPEC® Crossed-Roller Bearing Linear Translation Stages (Standard-Top Model)



Stock #66-453 **3 In Stock**

⊖ 1 ⊕ €665<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-2        | €665,00 each                  |
| Qty 3+         | €580,50 each                  |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

English **Type:**

**Physical & Mechanical Properties**

Linear (X) **Type of Movement:**



**30mm Standard-Top Stages - Center Drive**



**30mm Standard-Top Stages - Side Drive**



**40mm Standard-Top Stages - Center Drive**



**40mm Standard-Top Stages - Side Drive**



**70mm Standard-Top Stages - Center Drive**



**70mm Standard-Top Stages - Side Drive**



**125mm Standard-Top Stages - Center Drive**



**125mm Standard-Top Stages - Side Drive**

