

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 125mm, Side Drive, Standard Top, Metric Extended Micrometer



125mm Micrometer Drive Stage

Stock #66-461 ■ In Stock



1



€699,00

ADD TO CART

Qty 1-2

€699,00

Qty 3+

€611,80

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Crossed Roller Bearing

Type of Drive:
Metric Micrometer

Drive Orientation: Side Drive
Type: Metric
Stage Size (mm): 125 x 125
Travel (mm): 50
Center Hole: M6 x 1
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 20
Mounting Threads: (21) M6 x 1, (4) M3 x 0.5, (8) M2 x 0.4
Stage Size (inches): 4.92 x 4.92
Straight Line Accuracy (µm): 2
Pitch (arcsec): 40
Yaw (arcsec): 30

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)