


In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #23-136 3-4 DAYS



1



€115,00

ADD TO CART

Qty 1-5

€115,00

Qty 6+

€92,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number (v_d):
67.8

Bevel:
Protective as needed

Clear Aperture (%):
90

Clear Aperture CA (mm): 11.25 x 11.25
Dimensions (mm): 12.50 x 12.50 +0.00/-0.20
Thickness (mm): 1.50 ±0.10
Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)
Density (g/cm³): 2.20
Edges: Fine Ground
Index of Refraction n_d: 1.458
Knoop Hardness (kg/mm²): 522
Parallelism (arcsec): <5
Poisson's Ratio: 0.16
Substrate: Fused Silica (Corning 7980)
Surface Quality: 20-10
Transmitted Wavefront, P-V: λ/10
Type: Protective Window
Wavelength Range (nm): 200 - 2200
Young's Modulus (GPa): 73
Length (mm): 12.50
Width (mm): 12.50

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View