

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

12.5mm Square, 45° AOI, Hot Mirror



Hot Mirrors

Stock #62-624   In Stock



1



€38,00

ADD TO CART

Qty 1-9

€38,00

Qty 10+

€33,90

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°):  
45.00

Coating:  
Hot Mirror, 45°

Substrate: BOROFLOAT®

|                                                                               |
|-------------------------------------------------------------------------------|
| <b>Reflection (%):</b><br>>90, 750 - 1125nm                                   |
| <b>Dimensions (mm):</b><br>12.5 x 12.5                                        |
| <b>Surface Quality:</b><br>80-50                                              |
| <b>Thickness (mm):</b><br>1.10                                                |
| <b>Transmission (%):</b><br>>85, 425 - 675nm                                  |
| <b>Type:</b><br>Dichroic Filter                                               |
| <b>Dimensional Tolerance (mm):</b><br>±0.5                                    |
| <b>Coating Specification:</b><br>Surface 1: 45° Hot Mirror<br>Surface 2: None |
| <b>Wavelength Range (nm):</b><br>425 - 1125                                   |
| <b>Surface Flatness (P-V):</b><br>4 - 6λ                                      |
| <b>Coating Type:</b><br>Dielectric                                            |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Compliant</a>             |