

1.25X Mag, InfiniGage CW Precision Spacer

See More by [Infinity Photo-Optical Company](#)



Stock **#64-875** **3 In Stock**

-

1

+

€78⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€78,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Lens Accessory

Compatible Lens:

[#64-877](#)

Optical Properties

Horizontal Field of View, 1/2" Sensor:

5.1mm

Horizontal Field of View, 1/3" Sensor:

3.8mm	
	Working Distance (mm):
26.00	
	Magnification:
1.25X	

Threading & Mounting	
	Mount:
C-Mount	

Regulatory Compliance	
	RoHS 2015:
Compliant	
	Reach 224:
Compliant	
	Certificate of Conformance:
View	

Product Details

- Accurate Measurements Based on Field of View
 - 7 Spacer Options for a Wide Range of Magnifications
 - UV Option Available
- The InfiniGage™ main lens mates with seven precision spacers for multiple magnification and working distance choices. Simply set InfiniGage™ to the desired magnification and begin making accurate measurements. The Infinigage™ accepts 11.8mm to 12.5mm diameter filters for polarization or color analysis without changing outer dimensions. The InfiniGage™ can be doubled in magnification by simply adding a DL Doubler Tube, reducing the FOV by a factor of two. The Infinigage™ is also available in UV which is optimized for best performance from 250nm-700nm.
- Note:** InfiniGage™ CW option is only compatible with CW Precision Spacers.

Technical Information

	Magnification	Working Distance	Field of View on ½" Sensor	Field of View on 1/3" Sensor
InfiniGage Precision Spacer with 2X Amplifier (Optional)	0.25X	286mm	25.6mm	19.2mm
	0.5X	155mm	12.8mm	9.6mm
	0.66X	120mm	9.7mm	7.3mm
	1.0X	85mm	6.4mm	4.8mm
	1.3X	72mm	4.9mm	3.6mm
	1.5X	67mm	4.3mm	3.2mm
	2.0X	52mm	3.2mm	2.4mm