

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



Stock #15-402 3-4 DAYS



1



€110,00

ADD TO CART

Qty 1-5

€110,00

Qty 6+

€88,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number ( $v_d$ ):  
67.8

Bevel:  
Protective as needed

Clear Aperture (%):  
80

|                                                                                                                                        |
|----------------------------------------------------------------------------------------------------------------------------------------|
| <b>Clear Aperture CA (mm):</b><br>10.16                                                                                                |
| <b>Diameter (mm):</b><br>12.70 +0.00/-0.20                                                                                             |
| <b>Thickness (mm):</b><br>1.50 ±0.10                                                                                                   |
| <b>Coating:</b><br>Uncoated                                                                                                            |
| <b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b><br>0.52 (+5 to +35°C)<br>0.57 (0 to +200°C)<br>0.48 (-100 to +200°C) |
| <b>Density (g/cm³):</b><br>2.20                                                                                                        |
| <b>Edges:</b><br>Fine Ground                                                                                                           |
| <b>Index of Refraction n<sub>d</sub>:</b><br>1.458                                                                                     |
| <b>Knoop Hardness (kg/mm²):</b><br>522                                                                                                 |
| <b>Parallelism (arcsec):</b><br><5                                                                                                     |
| <b>Poisson's Ratio:</b><br>0.16                                                                                                        |
| <b>Substrate:</b><br><a href="#">Fused Silica</a> (Corning 7980)                                                                       |
| <b>Surface Quality:</b><br>20-10                                                                                                       |
| <b>Transmitted Wavefront, P-V:</b><br>λ/10                                                                                             |
| <b>Type:</b><br>Protective Window                                                                                                      |
| <b>Wavelength Range (nm):</b><br>200 - 2200                                                                                            |
| <b>Young's Modulus (GPa):</b><br>73                                                                                                    |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |