print-screen-header

12.7mm Dia. 488nm λ/2 Quartz Waveplate Multiple Order

Stock **#85-082** CLEARANCE 3-4 DAYS

- 1 + **€164,95**

ADD TO CART

Qty 1+

€164,95

Volume Pricing

Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
8.00

Coating:
Laser V-Coat (488nm)

Design Wavelength DWL (nm):
488

Diameter (mm):
12.70 +0.00/-0.25

Substrate:
Crystal Quartz

Retardance:
λ/2

Surface Quality:
10-5

Thickness (mm):
6.40 +0.00/-0.25

Type:
Crystalline Waveplate

Construction:
Crystalline

Transmitted Wavefront, P-V:
λ/10 for central 80% of clear aperture

Parallelism (arcsec):
<3

Retardance Tolerance:
±λ/200

Temperature Coefficient (λ/°C):
0.0015

Retardance Order:
Multiple Order

Regulatory Compliance

RoHS 2015:
Compliant

Reach 209:
Compliant

Certificate of Conformance:
View