

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

12.7 mm Dia. 632.8nm $\lambda/4$ Quartz waveplate Multiple Order



Stock #85-077 [CONTACT US](#)



1



€257,00

ADD TO CART

Qty 1-5

€257,00

Qty 6+

€208,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
8.00

Coating:
Laser V-Coat (632.8nm)

Design Wavelength DWL (nm):
632.8

Diameter (mm):

12.70 +0.00/-0.25
Substrate: Crystal Quartz
Retardance: λ/4
Surface Quality: 10-5
Thickness (mm): 6.40 +0.00/-0.25
Type: Crystalline Waveplate
Construction: Crystalline
Transmitted Wavefront, P-V: λ/10 for central 80% of clear aperture
Parallelism (arcsec): <3
Retardance Tolerance: ±λ/200
Temperature Coefficient (λ/°C): 0.0015
Retardance Order: Multiple Order

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View