

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

12.7mm Dia. UHR Broadband Dielectric Mirror, 750-1100nm



Stock #17-497 CLEARANCE 3-4 DAYS



1



€234,95

ADD TO CART

Qty 1+

€234,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):  
12.70 +0.00/-0.10

Surface Flatness (P-V):  
λ/10

Substrate:   
[Fused Silica](#) (Corning 7980)

Surface Quality:  
10-5

Coating Specification:  
R<sub>abs</sub> >99.9% @ 750 - 1100nm (45°, s-pol)

|                                                     |                                    |
|-----------------------------------------------------|------------------------------------|
| R <sub>abs</sub> >99.9% @ 750 - 1100nm (45°, p-pol) |                                    |
| Coating:                                            | UHR Dielectric Mirror (750-1000nm) |
| Coating Type:                                       | Dielectric                         |
| Angle of Incidence (°):                             | 45                                 |
| Clear Aperture CA (mm):                             | 9.20                               |
| Edges:                                              | Ground                             |
| Parallelism (arcmin):                               | <3                                 |
| Thickness (mm):                                     | 6.35 ±0.20                         |
| Type:                                               | Flat Mirror                        |
| Wavelength Range (nm):                              | 750 - 1100                         |

Regulatory Compliance

|                             |                      |
|-----------------------------|----------------------|
| RoHS:                       | Compliant            |
| Certificate of Conformance: | <a href="#">View</a> |