

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 12.7 mm Dia., Uncoated, Ultrarast Thin window



Stock #11-749 3-4 DAYS

-

1

+

 €95,00

ADD TO CART

Qty 1-5
€95,00
Qty 6+
€85,50
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
Uncoated

Diameter (mm):
12.70 +0.00/-0.10

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Index of Refraction n_d: 1.458
Surface Quality: 20-10
Thickness (mm): 1.00 ±0.10
Type: Ultrafast Window
Bevel: Protective as needed
Clear Aperture (%): 90
Transmitted Wavefront, P-V: $\lambda/6$
Abbe Number (v_d): 67.8
Parallelism (arcsec): ≤30
Wavelength Range (nm): 200 - 2200
Fused Silica Grade: 7979 0G
Edges: Fine Ground
Type of Window: Glass

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View