

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



TECHSPEC Laser Grade PCX Lenses

Stock #38-640 3-4 DAYS

[Other Coating Options](#)



1



€145,00

ADD TO CART

Qty 1-5

€145,00

Qty 6+

€116,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.70 +0.00/-0.025

Effective Focal Length EFL (mm):
200.00 @ 355nm

Back Focal Length BFL (mm):

197.35
Coating: Uncoated
Substrate: ☐ Fused Silica (Coming 7980)
Surface Quality: 10-5
Power (P-V) @ 632.8nm: λ
Irregularity (P-V) @ 632.8nm: $\lambda/10$
Focal Length Tolerance (%): ± 1
Centering (arcmin): <1
Center Thickness CT (mm): 4.00 $\pm$ 0.10
Edge Thickness ET (mm): 3.79
Radius R₁ (mm): 95.22
Clear Aperture CA (mm): 11.43
f/#: 15.75
Numerical Aperture NA: 0.03
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 200 - 2200

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View