

TECHSPEC®

12.7mm H x 12.7mm L x 12.5mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock #35-020 3-4 DAYS

- 1 + **€62,00**

ADD TO CART

Qty 1-5
€62,00

Qty 6+
€49,50

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
12.50

Substrate: ☐
[N-BK7](#)

f#:

0.984251968503937
Numerical Aperture NA: 0.51
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 8.15
Center Thickness CT (mm): 6.60
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 12.7 x 12.7
Edge Thickness ET (mm): 1.33
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 6.46
Surface Quality: 60-40

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View