

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC  
12.7mm H x 12.7mm L x 150mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock #35-023 3-4 DAYS

1 €62,00

ADD TO CART

Qty 1-5

€62,00

Qty 6+

€49,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):  
150.00

Substrate: ☐  
[N-BK7](#)

f#:

|                                                 |
|-------------------------------------------------|
| 11.8110236220472                                |
| <b>Numerical Aperture NA:</b><br>0.04           |
| <b>Coating:</b><br>Uncoated                     |
| <b>Type:</b><br>Cylinder Lens, Plano-Convex     |
| <b>Wavelength Range (nm):</b><br>350 - 2200     |
| <b>Back Focal Length BFL (mm):</b><br>148.25    |
| <b>Center Thickness CT (mm):</b><br>2.65        |
| <b>Center Thickness Tolerance (mm):</b><br>±0.1 |
| <b>Dimensional Tolerance (mm):</b><br>+0.0/-0.2 |
| <b>Dimensions (mm):</b><br>12.7 x 12.7          |
| <b>Edge Thickness ET (mm):</b><br>2.39          |
| <b>Focal Length Tolerance (%):</b><br>±3        |
| <b>Radius R<sub>1</sub> (mm):</b><br>77.52      |
| <b>Surface Quality:</b><br>60-40                |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |