

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



12mm Fixed Focal Length, #14-397

Stock #14-397 3-4 DAYS



1



€315,00

ADD TO CART

Qty 1+

€315,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Iris Option:
Variable

Length (mm):
41.62

Horizontal Field of View, 1/2" Sensor:
29.86°

Horizontal Field of View, 2/3" Sensor:
39.94°

Filter Thread:

M30.5 x0.50 (Female)
Maximum Diameter (mm): 32.5
Weight (g): 85
Horizontal Field of View, 1/3" Sensor: 22.62°
Maximum Image Circle (mm): 11.00
Horizontal Field of View @ Max Sensor Format: 39.94°
Type: Fixed Focal Length Lens
Focal Length FL (mm): 12.00
Maximum Sensor Format: 2/3"
Working Distance (mm): 100 - ∞
Mount: C-Mount
Aperture (f/#): f/1.4 - f/16
Distortion (%): <-1
Horizontal Field of View, 1/4" Sensor: 15.19°
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View