

TECHSPEC® 12mm Dia. x 15mm FL, Uncoated, Hybrid Asphere



TECHSPEC® Plastic Hybrid Aspheric Lenses

Stock **#21-224** [CONTACT US](#)

⊖ 1 ⊕ **€84,00**

ADD TO CART

Qty 1-24

€84,00

Qty 25+

€64,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.00 ±0.15

Effective Focal Length EFL (mm):
15.00 @ 587.6nm

Numerical Aperture NA:
0.40

Back Focal Length BFL (mm): 12.95
Substrate:  Zeonex K22R
Aspheric Design Wavelength (nm): 587.6
Coating: Uncoated
Surface Quality: 80-50
Clear Aperture CA (mm): 10.00
Edge Thickness ET (mm): 2.29
Center Thickness CT (mm): 3.70 ±0.20
f/#: 1.25
Bevel: Protective bevel as needed
Operating Temperature (°C): -30 to +70
Radius R ₂ (mm): 48.3
Shape of Back Surface: Convex
Type: Aspheric Lens
Wavelength Range (nm): 475 - 675
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View