

12mm Dia. x 48mm FL, Commercial Grade, Plano-Convex Lens



Stock **#23-075** CLEARANCE 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕ **€19,95**

ADD TO CART

Qty 1+

€19,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.00 +0.00/-0.10

Effective Focal Length EFL (mm):
48.00

Back Focal Length BFL (mm):
46.69

Coating:
MgF₂ (400-700nm)

Coating Specification:

R _{avg} ≤1.75% @ 400 - 700nm	
Substrate:	N-BK7
Focal Length Tolerance (%):	±1
Centering (arcmin):	6.00
Edge Thickness ET (mm):	1.26
Radius R ₁ (mm):	24.81
Clear Aperture CA (mm):	≥10.2
f/#:	4.00
Numerical Aperture NA:	0.13
Type:	Plano-Convex Lens

Regulatory Compliance

RoHS:	Compliant
Certificate of Conformance:	View