

12mm Dia x -6.1mm FL Protected Gold Coated, Convex Mirror



Stock **#64-069** 3-4 DAYS

- 1 + **€45,50**

ADD TO CART

Qty 1-5
€45,50

Qty 6+
€41,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.00 +0.00/-0.10

Focal Length FL (mm):
-6.10

Center Thickness CT (mm):
3.00

Clear Aperture (%):

Coating: Protected Gold (700-10000nm)
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating Type: Metal
Edge Thickness ET (mm): 1.41
Focal Length Tolerance (%): ±2
Radius R (mm): 12.11
Substrate: ☐ NSF5
Surface Quality: 60-40
Type: Spherical Mirror
Wavelength Range (nm): 700 - 10000
Damage Threshold, Reference: ☐ 0.8 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant