

TECHSPEC® 12mm Diameter x -15 FL, VIS 0° Coated, Plano-Concave Lens



Stock **#48-691** 3-4 DAYS

[Other Coating Options](#)

- 1 + **€42,00**

ADD TO CART

Qty 1-9
€42,00
Qty 10+
€37,75
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.00 +0.0/-0.025

Effective Focal Length EFL (mm):

-15.00
Substrate: NSF11
f#: 1.25
Numerical Aperture NA: 0.40
Coating: VIS 0° (425-675nm)
Type: Plano-Concave Lens
Wavelength Range (nm): 425 - 675
Back Focal Length BFL (mm): -16.68
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.00
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <1
Clear Aperture CA (mm): 11.00
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Edge Thickness ET (mm): 4.47
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁ (mm): -11.77
Surface Quality: 40-20
Damage Threshold, By Design: 5 J/cm² @ 532nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant