

# 12" Diameter, Parabolic Reflector



Stock #53-875 ☐ In Stock

-

1

+

 €63,00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| €63,00                        |
| Qty 11+                       |
| €56,70                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: ☐  
Aluminum

Diameter (inches):  
12.0

Diameter (mm):  
304.80

Effective Focal Length EFL (inches):

|                                                  |
|--------------------------------------------------|
| 3.0                                              |
| <b>Effective Focal Length EFL (mm):</b><br>76.20 |
| <b>Radius of Curvature (mm):</b><br>152.40       |
| <b>Coating:</b><br>Uncoated                      |
| <b>Coating Type:</b><br>Uncoated                 |
| <b>Center Hole Diameter (inches):</b><br>0.75    |
| <b>Height (mm):</b><br>72.39                     |
| <b>Thickness (inches):</b><br>0.04               |
| <b>Thickness (mm):</b><br>1.02                   |
| <b>Type:</b><br>Parabolic Mirror                 |
| <b>Weight (kg):</b><br>0.267                     |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |